



YDS7K6, Copper Full Tension Splice

By Burndy
Catalog # [YDS7K6](#)

CU Full Tension Splice, Accommodates Wire: 1/2 COPPERWELD,
Die Index: 260

Features

- Copper Full Tension Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - CopperWeld Str Size	3/0 F AWG
---------------------------------	-----------

Configuration

Physical Attribute - Number of Crimps Required	4
Connector Type	Splice

Dimensions

Dimension - L Length Overall	219 mm
------------------------------	--------

Dimension - B Length inch	3.62 in
Dimension - Outside Diameter inch	1.22 in
Dimension - Length Overall inch	8.63 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	260
UPC	781810014592
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014592

Logistics

Minimum Pack Quantity	1
Pallet Quantity	480
Carton Quantity	8

Product Assets

[Catalog \[English\]](#)