

YDS7K7, Copper Full Tension Splice

By Burndy
Catalog # [YDS7K7](#)



CU Full Tension Splice, Accommodates Wire: 7/16 COPPERWELD,
Die Index: 328

Features

- Copper Full Tension Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - CopperWeld Str Size	2/0 F AWG
---------------------------------	-----------

Configuration

Physical Attribute - Number of Crimps Required	3
Connector Type	Splice

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in
Dimension - L Length Overall	157 mm
Dimension - B Length inch	2.79 in
Dimension - Outside Diameter inch	1.11 in
Dimension - Length Overall inch	6.20 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	328
UPC	781810014608
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810014608

Logistics

Minimum Pack Quantity	20
Pallet Quantity	980
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)