



YDS7M10T, Full Tension Sleeve for Alumoweld

By Burndy
Catalog # [YDS7M10T](#)



Full Tension Sleeve for Alumoweld, 7 #10 AWG, 3 #7 AWG, 676 Index

Features

- Full Tension Sleeve for Alumoweld

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	RUS
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AWAC Size	• 4 • 3
Conductor - Alumoweld Size	7 #10

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	4-22/25 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	252 mm
Dimension - B Length inch	4.88 in
Dimension - Outside Diameter inch	0.71 in
Dimension - Length Overall inch	9.91 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	• 676 • 721
UPC	781810015469
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00781810015469

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4200
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)