



YDS7M6T, Full Tension Sleeve for Alumoweld

By Burndy
Catalog # [YDS7M6T](#)



Full Tension Sleeve for Alumoweld, 7 #6 AWG, 679 or 726 Index

Features

- Full Tension Sleeve for Alumoweld

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AWAC Size	1 1/0 2/0
Conductor - Alumoweld Size	7#6
Conductor Type	AWAC

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - B Length fraction	7-13/25 in
-------------------------------	------------

Dimension - L Length Overall	385 mm
Dimension - B Length inch	7.52 in
Dimension - Outside Diameter	1.07 in
Dimension - Length Overall	15.17 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	679 726
UPC	781810015476
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00781810015476

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1600
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)