



YDS7M7T, Full Tension Sleeve for Alumoweld

By Burndy
Catalog # [YDS7M7T](#)



Full Tension Sleeve for Alumoweld, 7 #7 AWG, 678 Index

Features

- Full Tension Sleeve for Alumoweld

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	RUS
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AWAC Size	• 2 • 1 • 1/0
Conductor - Alumoweld Size	7#7

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - B Length fraction	7-11/50 in
-------------------------------	------------

Dimension - L Length Overall	370 mm
Dimension - B Length inch	7.22 in
Dimension - Outside Diameter	0.98 in
Dimension - Length Overall	14.56 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	• 678 • 726
UPC	781810015445
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00781810015445

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2340
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)