



YDS7M8T, Aluminum Full Tension Sleeve

By Burndy
Catalog # [YDS7M8T](#)



Al Full Tension Sleeve, Overlap Crimps, 7 #8,3 #5(Alumoweld),
12.21" L, 668 or 723 Index

Features

- Aluminum Full Tension Sleeve

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	RUS
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AWAC Size	2
Conductor - Alumoweld Size	7#8 3#5

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	6-1/33 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	310 mm
Dimension - B Length inch	6.03 in
Dimension - Outside Diameter inch	0.88 in
Dimension - Length Overall inch	12.21 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	668 723
UPC	781810015421
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00781810015421

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3360
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)