



YDS8KT, Copper, Single Sleeve Full Tension Splice

By Burndy
Catalog # [YDS8KT](#)



CU Full Tension Splice, Accommodates Wire: 8A COPPERWELD,
Die Index: 162 or 202

Features

- Copper Single Sleeve Full Tension Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	RUS
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - CopperWeld Str Size	8 A AWG
---------------------------------	---------

Configuration

Physical Attribute - Number of Crimps Required	4
Connector Type	Splice

Dimensions

Dimension - Pin Diameter inch	0.41 in
Dimension - Pin Diameter fraction	2/5 in

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	122 mm
Dimension - B Length inch	2.31 in
Dimension - Length Overall inch	4.80 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	162 202
UPC	781810820681
Prefilled Oxide Inhibitor	N
Material	Copper
Plating Type	Unplated
UPC 14 Digit GTIN	00781810820681

Logistics

Minimum Pack Quantity	1
Pallet Quantity	11600
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)