




YDS8WG1, Copper, Single Sleeve Full Tension Splice

By Burndy
Catalog # [YDS8WG1](#)

CU Full Tension Splice, Accommodates Wire: #8 Cu Sol (Hard, Medium, or Soft Drawn), Die Index: 161



Features

- Copper Single Sleeve Full Tension Splice
- Full Rated Breaking Strength of Hard, Medium, or Soft Drawn Solid Copper Conductor

Application

For Solid Copper Conductors

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	8 AWG
-------------------------------	-------

Configuration

Physical Attribute - Number of	1
Crimps Required	
Connector Type	Splice

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	48 mm
Dimension - B Length inch	0.91 in
Dimension - Outside Diameter	0.31 in
Dimension - Length Overall	1.88 in

General

Trade Name	HYSPLICE™
Sub Brand	HYSPLICE
Die Index	161
Oxide Inhibitor Type	Penetrox E
UPC	781810014615
Type	YDS-W
Prefilled Oxide Inhibitor	Y
Material	Copper
UPC 14 Digit GTIN	00781810014615

Logistics

Minimum Pack Quantity	1
Pallet Quantity	57600
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)