



YDSR25RL, Aluminum Extra Long Replacement Splice

By Burndy
Catalog # [YDSR25RL](#)

Al Tension Single Sleeve UniSplice, 1/0(ACSR,AAAC,AAC)



Features

- Aluminum Extra Long Replacement Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Size	1/0 AWG
Conductor - AAAC 6201 Size	1/0 AWG
Conductor - AL Str Size	1/0 AWG
Conductor - AAAC 5005 Size	1/ 0 AWG
Conductor Type	- ACSR C Str-Size - AL C Str-Size
Conductor - ACSR Str Size	1/0 (6/1) Raven AWG

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Length	34.13 in
Dimension - L Length Overall mm	867 mm

Dimension - B Length inch	6.88 in
Dimension - Outside Diameter inch	.80 in
Height	0.8 in
Width	0.8 in
Dimension - Length Overall inch	34.13 in
Dimensions	34.13 in x 0.8 in x 0.8 in

General

Plated	N
Trade Name	UNISPLICE™
Die Index	- C 167 247 660 702
UPC	781810488409
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00781810488409

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)