



YDSR26RL, Aluminum Extra Long Replacement Splice

By Burndy
Catalog # [YDSR26RL](#)

Al Tension Single Sleeve UniSplice, 2/0(ACSR,AAC,5005,AAAC)



Features

- Aluminum Extra Long Replacement Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Cmpt Size Range	2/0 AWG
Conductor - ACSR Cmpt Size	2/0 AWG
Conductor - AAAC 6201 Size	2/0 AWG
Conductor - AAAC 5005 Size	2/0 AWG
Conductor Type	- ACSR C Str-Size - AL C Str-Size

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Length	35.5 in
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in
Dimension - L Length Overall	902 mm
Dimension - B Length inch	6.70 in
Dimension - Outside Diameter inch	.83 in
Height	0.83 in
Width	0.83 in
Dimension - Length Overall inch	35.50 in
Dimensions	35.5 in x 0.83 in x 0.83 in

General

Plated	N
Trade Name	UNISPLICE™
Die Index	659
UPC	781810503232
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00781810503232

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)



A Hubbell brand