



YDSR27RL, Aluminum Extra Long Replacement Splice

By Burndy
Catalog # [YDSR27RL](#)

Al Tension Single Sleeve UniSplice, 3/0(ACSR,AAC,AAAC)



Features

- Aluminum Extra Long Replacement Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AAAC 6201 Size	3/0 AWG
Conductor - AL Str Size	3/0 AWG
Conductor - AAAC 5005 Size	3/0 AWG
Conductor Type	- ACSR C Str-Size - AL C Str-Size
Conductor - ACSR Str Size	3/0 AWG

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Length	42.25 in
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in
Dimension - L Length Overall	1073 mm
Dimension - B Length inch	9.03 in
Dimension - Outside Diameter	.91 in
inch	
Height	0.91 in
Width	0.91 in
Dimension - Length Overall	42.25 in
inch	
Dimensions	42.25 in x 0.91 in x 0.91 in

General

Plated	N
Trade Name	UNISPLICE™
Die Index	658
UPC	781810503263
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00781810503263

Logistics

Minimum Pack Quantity	1
Pallet Quantity	540
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)