



YDSR2RL, Extra Long Replacement Splice

By Burndy
Catalog # [YDSR2RL](#)

Al Tension Single Sleeve UniSplice, #2(ACSR,AAC,5005,AAAC)



Features

- Aluminum Extra Long Replacement Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AAAC 6201 Size	2 AWG
Conductor - AL Str Size	2 AWG
Conductor - AAAC 5005 Size	2 AWG
Conductor Type	- ACSR C Str-Size - AL C Str-Size
Conductor - ACSR Str Size	2 AWG

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Length	28 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall	711 mm
Dimension - B Length inch	5.04 in
Dimension - Outside Diameter	.66 in
inch	
Height	0.66 in
Width	0.66 in
Dimension - Length Overall	28.00 in
inch	
Dimensions	28 in x 0.66 in x 0.66 in

General

Plated	N
Trade Name	UNISPLICE™
Die Index	- BG 687 243
UPC	781810503188
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00781810503188

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1080
Carton Quantity	30

Product Assets

[Catalog \[English\]](#)