



YDSR321RL, Aluminum Extra Long Replacement Splice

By Burndy
Catalog # [YDSR321RL](#)

Al Tension Single Sleeve UniSplice, 336.4(ACSR,AAC)



Features

- Aluminum Extra Long Replacement Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	336.4 KCMIL
Conductor Type	- ACSR C Str-Size - AL C Str-Size
Conductor - ACSR Str Size	336.4 KCMIL

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Length	45.75 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall	1162 mm
Dimension - B Length inch	9.06 in
Dimension - Outside Diameter inch	1.13 in
Height	1.13 in
Width	1.13 in
Dimension - Length Overall inch	45.75 in
Dimensions	45.75 in x 1.13 in x 1.13 in

General

Plated	N
Trade Name	UNISPLICE™
Die Index	655
UPC	781810503287
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00781810503287

Logistics

Minimum Pack Quantity	1
Pallet Quantity	324
Carton Quantity	9

Product Assets

[Catalog \[English\]](#)