



YDSR341RL, Extra Long Replacement Splice

By Burndy
Catalog # [YDSR341RL](#)

Extra long replacement splice designed to facilitate the permanent replacement of an existing line splice. Eliminates need for two splices and extra conductor.

Features

- Extra Long Replacement Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AAAC 5005 Size	419.6 KCMIL
Conductor Type	- ACSR C Str-Size - AL C Str-Size
Conductor - ACSR Str Size	397.5 KCMIL

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Length	49.5 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in



Dimension - L Length Overall mm	1257 mm
Dimension - B Length inch	10.12 in
Dimension - Outside Diameter inch	1.30 in
Height	1.3 in
Width	1.3 in
Dimension - Length Overall inch	49.50 in
Dimensions	49.5 in x 1.3 in x 1.3 in

General

Plated	N
Trade Name	UNISPLICE™
Die Index	327
UPC	781810503294
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00781810503294

Logistics

Minimum Pack Quantity	1
Pallet Quantity	96
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)



A Hubbell brand