



YDSR361RL, Aluminum Extra Long Replacement Splice

By Burndy
Catalog # [YDSR361RL](#)

Al Tension Replacement Single Sleeve UniSplice



Features

- Aluminum Extra Long Replacement Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size	477 kcmil, 556.5 kcmil
Conductor Type	- ACSR C Str-Size - AL C Str-Size

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Length	51.25 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall	1302 mm
mm	
Dimension - B Length inch	11.75 in
Dimension - Outside Diameter	1.40 in
inch	
Height	1.4 in
Width	1.4 in
Dimension - Length Overall	51.25 in
inch	
Dimensions	51.25 in x 1.4 in x 1.4 in

General

Plated	N
Trade Name	UNISPLICE™
Die Index	788
UPC	781810500200
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 14 Digit GTIN	00781810500200

Logistics

Minimum Pack Quantity	1
Pallet Quantity	25
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)