



YE25G49, Compression Terminal Plug, 1/0 AWG

By Burndy
Catalog # [YE25G49](#)



Terminal plug, 1/0 AWG, 600V-35KV,Tin plated

Features

- Compression Terminal Plug, Oil and Water-Tight
- Shrouded, tin-plated, Copper Barrel and Brazed Plug

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	1/0 AWG
Conductor - Copper Str	1/0 AWG
Compact Size	
Conductor Size	1/0 AWG
Conductor Type	CODE
Conductor - Copper Str Size	1/0
Range	

Configuration

Connector Type	INLINE PIN
----------------	------------

Current

Voltage - Maximum	35000
-------------------	-------

Dimensions

Package Height	0.000 in
----------------	----------

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - P inch	3.00 in
Dimension - L Length Overall	117 mm
mm	
Dimension - Outside Diameter	0.51 in
inch	
Dimension - B Length fraction	1-1/8 in
Dimension - B Length inch	1.12 in
Dimension - Length Overall	4.62 in
inch	

General

Trade Name	HYSEALPLUG™
Insulation	Y
Feature - Barrel Style	Shrouded
Plated	Y
Sub Brand	Pin Terminals, HYSEALPLUG
UPC	781810053409
Type	YE
Construction Material - Main	Copper
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810053409
UPC 14 Digit GTIN	00781810053409

Logistics

Minimum Pack Quantity	1
Pallet Quantity	12000
Carton Quantity	100

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)