



YE25LH97, Compression Terminal Plug, Oil/Water Tight with Shroud, Tin-Plated, 1/0 Str

By Burndy
Catalog # [YE25LH97](#)

Oil and water-tight terminal with shrouded, tin-plated,CU barrel and brazed plug Used for terminating insulated CU conductor at cutout or transformer,11.38 IN L.

Features

- Oil and water-tight terminal with shroud, tin-plated copper barrel and brazed plug
- For terminating insulated copper conductor at cutout or transformer

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	1/0 AWG
Conductor - Copper Str	1/0 AWG
Compact Size	
Conductor Size	1/0 AWG
Conductor Type	CODE
Conductor - Copper Str Size Range	1/0

Configuration

Connector Type	INLINE PIN
----------------	------------

Current

Voltage - Maximum	35000
-------------------	-------

Dimensions



Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - P inch	8.06 in
Dimension - L Length Overall	283 mm
mm	
Dimension - B Length fraction	2-5/8 in
Dimension - B Length inch	2.62 in
Dimension - Inside Diameter	0.98 in
inch	
Dimension - Length BB inch	1.00 in
Dimension - Length Overall	11.13 in
inch	

General

Trade Name	HYSEALPLUG™
Die Index	163
Insulation	Y
Feature - Barrel Style	Shrouded
Plated	Y
Sub Brand	HYSEALPLUG
UPC	781810023365
Type	Shrouded Pin Terminals
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810023365
UPC 14 Digit GTIN	00781810023365

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4200
Carton Quantity	25

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand