



YE25R25, Aluminum Terminal Plug

By Burndy
Catalog # [YE25R25](#)



Terminal Plug for AL and ACSR, 1/0 AL, 1/0 ACSR, 4.62 in Length, Tin Plated, Yellow, BG or 5/8-1 or 243 or 8A Index

Features

- Aluminum HYPLUG with tin-plated copper plug for terminating aluminum or ACSR cable at cut-out, transformer and arrestor
- Plug may be bent to desired angle for easier insertion
- Terminals are Pre-Filled with PENETROX A-13 Joint Compound and sealed with color coded end caps

Application

for terminating aluminum or ACSR cable at cut-out, transformer and arrestor.

Specifications

Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	1/0 (6/1) Raven AWG
Conductor - ACSR Str Size Range	1/0 (6/1) Raven AWG
Conductor - AL Str Size	1/0 AWG
Conductor - AL Str Size Range	1/0 AWG

Dimensions

Package Length	0.000 in
----------------	----------

Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall	117 mm
Dimension - P inch	2.50 in
Package Height	0.000 in
Dimension - Length Overall	4.625 in
inch	

General

Die Index	• K-5/8-1 • 243 • BG • 8A
Trade Name	HYPLUG™
Prefilled Oxide Inhibitor	N
Sub Brand	HYPLUG
Color Code	Yellow
Plated	Y
Type	YE-R
UPC 14 Digit GTIN	00781810154151
Material	Aluminum
Plating Type	Tin
UPC	781810154151

Logistics

Minimum Pack Quantity	1
Carton Quantity	25
Pallet Quantity	24000

Product Assets

[Catalog \[English\]](#)