



YE26LH88, Compression Terminal Plug, Oil/Water Tight with Shroud, 2/0 Str

By Burndy
Catalog # [YE26LH88](#)

Terminal plug, 2/0 str



Features

- Oil and water-tight terminal with shroud, tin-plated copper barrel and brazed plug
- For terminating insulated copper conductor at cutout or transformer

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str	2/0 AWG
Compact Size	
Conductor Size	2/0 AWG
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Size	2/0 AWG
Range	
Conductor - Copper Str Size	2/0 AWG

Configuration

Connector Type	INLINE PIN
----------------	------------

Current

Voltage - Maximum	35000
-------------------	-------

Dimensions

Package Height	0.000 in
----------------	----------

Dimension - B Length fraction	2-1/2 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - P inch	8.06 in
Dimension - L Length Overall	289 mm
mm	
Dimension - B Length inch	2.48 in
Dimension - Inside Diameter	0.73 in
inch	
Dimension - Length BB inch	1.00 in
Dimension - Length Overall	11.38 in
inch	

General

Feature - Barrel Style	Shrouded
Plated	Y
Trade Name	HYSEALPLUG™
Die Index	241
UPC	781810023372
Type	Shrouded Pin Terminals
Insulation	Y
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810023372
UPC 14 Digit GTIN	00781810023372

Logistics

Minimum Pack Quantity	25
Pallet Quantity	4200
Carton Quantity	25

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand