

# YE26R60, Aluminum Terminal Plug

By Burndy  
Catalog # [YE26R60](#)



Aluminum HYPLUG™ Connector, 2/0 Str. Al 2/0 ACSR, 9-1/2 in L, Terminal Plug for Aluminum and ACSR

### Features

- Aluminum HYPLUG with tin-plated copper plug for terminating aluminum or ACSR cable at cut-out, transformer and arrestor
- Plug may be bent to desired angle for easier insertion
- Terminals are Pre-Filled with PENETROX A-13 Joint Compound and sealed with color

### Application

For Terminating Aluminum Or ACSR Cable At Cut-Out, Transformer And Arrestor

### Specifications

|                                    |                                                      |
|------------------------------------|------------------------------------------------------|
| Buy American Compliant             | No                                                   |
| Certification - cULus              | No                                                   |
| EU RoHS Indicator                  | Yes                                                  |
| Certification - UL Recognized      | No                                                   |
| Buy America(n) Qualified           | BABA Compliant (All status valid till December 2025) |
| Certification - ETL                | No                                                   |
| Standards - RoHS Compliance Status | CM                                                   |
| Certification - CSA Approved       | No                                                   |
| UL Listed                          | No                                                   |

### Conductor

|                                 |                     |
|---------------------------------|---------------------|
| Conductor - ACSR Str Size       | 2/0 (6/1) Quail AWG |
| Conductor - ACSR Str Size Range | 2/0 (6/1) Quail AWG |
| Conductor - AL Str Size         | 2/0 AWG             |
| Conductor - AL Str Size Range   | 2/0 AWG             |

### Dimensions

|                              |           |
|------------------------------|-----------|
| Package Length               | 0.000 in  |
| Package Width                | 0.000 in  |
| Package Weight               | 0.000 lb. |
| Dimension - L Length Overall | 241 mm    |
| Dimension - P inch           | 6 in      |
| Package Height               | 0.000 in  |
| Dimension - Length Overall   | 9.50 in   |
| inch                         |           |

### General

|                           |                                                                                   |
|---------------------------|-----------------------------------------------------------------------------------|
| Die Index                 | <ul style="list-style-type: none"><li>• 249</li><li>• 840</li><li>• 11A</li></ul> |
| Trade Name                | HYPLUG™                                                                           |
| Prefilled Oxide Inhibitor | N                                                                                 |
| Sub Brand                 | HYPLUG                                                                            |
| Color Code                | Gray                                                                              |
| Plated                    | Y                                                                                 |
| Type                      | YE-R                                                                              |
| UPC 14 Digit GTIN         | 00781810154205                                                                    |
| Material                  | Aluminum                                                                          |
| Plating Type              | Tin                                                                               |
| UPC                       | 781810154205                                                                      |

### Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 1    |
| Carton Quantity       | 25   |
| Pallet Quantity       | 4200 |

### Product Assets

[Catalog \[English\]](#)