



YE27R60, Aluminum Terminal Plug

By Burndy
Catalog # [YE27R60](#)



Aluminium HYPLUG™ Connector, 3/0 Str. Al 3/0 ACSr, 9-1/2 in L, Terminal Plug for Aluminum and ACSr

Features

- Aluminum HYPLUG with tin-plated copper plug for terminating aluminum or ACSr cable at cut-out, transformer and arrestor
- Plug may be bent to desired angle for easier insertion
- Terminals are Pre-Filled with PENETROX A-13 Joint Compound and sealed with color

Application

For Terminating Aluminum Or ACSr Cable At Cut-Out, Transformer And Arrestor

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSr Str Size	3/0 (6/1) Pigeon AWG
Conductor - ACSr Str Size Range	3/0 (6/1) Pigeon AWG
Conductor - AL Str Size	3/0 AWG

Dimensions

Package Length	0.000 in
----------------	----------

Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.91 in
Dimension - L Length Overall mm	241 mm
Dimension - P inch	6 in
Package Height	0.000 in
Dimension - Length Overall inch	9.50 in

General

Die Index	• 249 • 840 • 11A
Trade Name	HYPLUG™
Prefilled Oxide Inhibitor	N
Sub Brand	HYPLUG
Color Code	Black
Plated	Y
Type	YE-R
UPC 14 Digit GTIN	00781810154250
Material	Aluminum
Plating Type	Tin
UPC	781810154250

Logistics

Minimum Pack Quantity	25
Carton Quantity	25
Pallet Quantity	4200

Product Assets

[Catalog \[English\]](#)