



YE28R60, Aluminum Terminal Plug

By Burndy
Catalog # [YE28R60](#)



Terminal Plug for AL and ACSR, 4/0 AL, 4/0 ACSR, 9.5 in Length, Tin Plated, Pink, 840 or 249 or 11A Index

Features

- Aluminum HYPLUG with tin-plated copper plug for terminating aluminum or ACSR cable at cut-out, transformer and arrestor
- Plug may be bent to desired angle for easier insertion
- Terminals are Pre-Filled with PENETROX A-13 Joint Compound and sealed with color

Application

For Terminating Aluminum Or ACSR Cable At Cut-Out, Transformer And Arrestor

Specifications

Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	4/0 (6/1) Penquin AWG
Conductor - ACSR Str Size Range	4/0 (6/1) Penquin AWG
Conductor - AL Str Size	4/0 AWG
Conductor - AL Str Size Range	4/0 AWG

Dimensions

Package Length	0.000 in
----------------	----------

Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter	0.91 in
inch	
Dimension - L Length Overall	241 mm
mm	
Dimension - P inch	6 in
Package Height	0.000 in
Dimension - Length Overall	9.50 in
inch	

General

Die Index	• 249 • 840 • 11A
Trade Name	HYPLUG™
Prefilled Oxide Inhibitor	N
Sub Brand	HYPLUG
Color Code	Pink
Plated	Y
Type	YE-R
UPC 14 Digit GTIN	00781810154304
Material	Aluminum
Plating Type	Tin
UPC	781810154304

Logistics

Minimum Pack Quantity	1
Carton Quantity	25
Pallet Quantity	4200

Product Assets

[Catalog \[English\]](#)