

YE2CLH128, Compression Terminal Plug, Oil/Water Tight with Shroud, #2 Str

By Burndy
Catalog # [YE2CLH128](#)

Terminal plug, 2 str



Features

- Oil and water-tight terminal with shroud, tin-plated copper barrel and brazed plug
- For terminating insulated copper conductor at cutout or transformer

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str	2 AWG
Compact Size	
Conductor Size	2 AWG
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Size	2 AWG
Range	
Conductor - Copper Str Size	2 AWG

Configuration

Connector Type	INLINE PIN
----------------	------------

Current

Voltage - Maximum	35000
-------------------	-------

Dimensions

Package Height	0.000 in
----------------	----------

Dimension - B Length fraction	2-1/8 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - P inch	6.06 in
Dimension - L Length Overall	229 mm
mm	
Dimension - B Length inch	2.12 in
Dimension - Inside Diameter	0.58 in
inch	
Dimension - Length BB inch	0.75 in
Dimension - Length Overall	9.00 in
inch	

General

Feature - Barrel Style	Shrouded
Plated	Y
Trade Name	HYSEALPLUG™
Die Index	162
UPC	781810023341
Type	Shrouded Pin Terminals
Insulation	Y
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810023341
UPC 14 Digit GTIN	00781810023341

Logistics

Minimum Pack Quantity	50
Pallet Quantity	12000
Carton Quantity	50

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)