



YE2CLH129, Compression Terminal Plug, Oil/Water Tight with Shroud, #2 Str

By Burndy
Catalog # [YE2CLH129](#)



Oil and water-tight terminal with shrouded,tin plated, CU barrel and brazed plug for terminating insulated CU conductor at cutout or transformer,Conductor:2 STR.

Features

- Oil and water-tight terminal with shroud, tin-plated copper barrel and brazed plug
- For terminating insulated copper conductor at cutout or transformer

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	2 AWG
Conductor - Copper Str	2 AWG
Compact Size	
Conductor Size	2 AWG
Conductor Type	CODE
Conductor - Copper Str Size	2 AWG
Range	

Configuration

Connector Type	INLINE PIN
----------------	------------

Current

Voltage - Maximum	35000
-------------------	-------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - P inch	6.06 in
Dimension - L Length Overall	229 mm
mm	
Dimension - B Length fraction	2-3/8 in
Dimension - B Length inch	2.38 in
Dimension - Inside Diameter	0.91 in
inch	
Dimension - Length BB inch	0.75 in
Dimension - Length Overall	9.00 in
inch	

General

Trade Name	HYSEALPLUG™
Die Index	162
Insulation	Y
Feature - Barrel Style	Shrouded
Plated	Y
Sub Brand	HYSEALPLUG
UPC	781810023358
Type	Shrouded Pin Terminals
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810023358
UPC 14 Digit GTIN	00781810023358

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4200
Carton Quantity	25

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)