YE2R25, Aluminum Terminal Plug

By Burndy
Catalog # YE2R25

Terminal Plug for AL and ACSR, #1-#2 AL, #2 ACSR, 4.62 in Length, Tin Plated, Orange, BG or 5/8-1 or 243 or 8A Index

Features

- Aluminum HYPLUG with tin-plated copper plug for terminating aluminum or ACSR cable at cut-out, transformer and arrestor
- Plug may be bent to desired angle for easier insertion
- Terminals are Pre-Filled with PENETROX A-13 Joint Compound and sealed with color coded end caps

Application

For Terminating Aluminum Or ACSR Cable At Cut-Out, Transformer And Arrestor

Specifications

Buy American Compliant	No
EU RoHS Indicator	Yes
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No

Conductor

Conductor - ACSR Str Size	• 2 (6/1) Sparrow AWG • 2 (7/1) Sparate AWG
Conductor - ACSR Str Size Range	2 (6/1) Sparrow AWG-2 (7/1) Sparate AWG
Conductor - AL Str Size	• 2 AWG • 1 AWG
Conductor - AL Str Size Range	2 AWG-1 AWG

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter inch	0.65 in
Dimension - L Length Overall mm	117 mm
Dimension - P inch	2.50 in
Package Height	0.000 in
Dimension - Length Overall inch	4.625 in

General

Die Index	• K-5/8-1 • 243 • BG • 8A
Trade Name	HYPLUG™
Prefilled Oxide Inhibitor	N
Sub Brand	HYPLUG
Color Code	Orange
Plated	Y
Type	YE-R
UPC 14 Digit GTIN	00781810154106
Material	Aluminum
Plating Type	Tin
UPC	781810154106

Logistics

Minimum Pack Quantity	1
Carton Quantity	25
Pallet Quantity	24000

Product Assets

Catalog [English]

© 2026 Hubbell Incorporated. All rights reserved