



YE30LH89, Compression Terminal Plug, Oil/Water Tight with Shroud

By Burndy

Catalog # YE30LH89

Terminal plug



Features

- Oil and water-tight terminal with shroud, tin-plated copper barrel and brazed plug
- For terminating insulated copper conductor at cutout or transformer

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Flex G Size	4/0 AWG
Conductor - Copper Str	300 KCMIL
Compact Size	
Conductor Size	300 KCMIL
Conductor - Copper Flex H Size	4/0 AWG
Conductor - Copper Flex G Size	4/0 AWG
Range	
Conductor - Material	COPPER
Conductor - Copper Flex K Size	4/0 AWG
Range	
Conductor - Copper Flex K Size	4/0 AWG
Conductor - Copper Flex M Size	4/0 AWG
Range	
Conductor - Copper Flex M Size	4/0 AWG
Conductor Type	CODE
Conductor - Copper Str Size	300 KCMIL
Conductor - Copper Flex H Size	4/0 AWG
Range	
Conductor - Copper Flex I Size	4/0 AWG
Conductor - Copper Flex I Size	4/0 AWG
Range	

Configuration

Connector Type INLINE PIN

Current

Voltage - Maximum	35000
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	1-1/16 in
Package Weight	0.000 lb.
Dimension - Width inch	0.91 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - P inch	4.00 in
Dimension - L Length Overall mm	184 mm
Dimension - B Length inch	1.09 in
Dimension - Length BB inch	1.00 in
Dimension - Length Overall inch	7.25 in

General

Feature - Barrel Style	Shrouded
Plated	Y
Trade Name	HYLUG™
Die Index	166
UPC	781810023433
Type	Shrouded Pin Terminals
Insulation	Y
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810023433
UPC 14 Digit GTIN	00781810023433

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3750
Carton Quantity	25

Operational

Temperature Rating 194

Product Assets

[Catalog \[English\]](#)

A Hubbell brand