

YE30R60, Aluminum Terminal Plug

By Burndy
Catalog # [YE30R60](#)



Aluminium Hyplug Connector, 266.8-336.4 kcmil Al, 266.8 kcmil
ACSR, 10.66 IN L

Features

- Aluminum Terminal Plug

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor Size	266.8 kcmil, 336.4 kcmil
Conductor - ACSR Str Size	• 266.8 (18/1) Waxwing kcmil • 266.8 (26/7) Owl kcmil
Conductor - ACSR Str Size Range	266.8 (18/1) Waxwing kcmil- 266.8 (26/7) Owl kcmil

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall	270 mm
mm	

Dimension - P inch	6 in
Package Height	0.000 in
Dimension - Length Overall	10.625 in
inch	

General

Die Index	• 317 • 705 • K-1-1/8-1
Color Code	Blue
Trade Name	HYPLUG™
Plated	Y
Prefilled Oxide Inhibitor	N
UPC 14 Digit GTIN	00781810154359
Material	Aluminum
Plating Type	Tin
UPC	781810154359

Logistics

Minimum Pack Quantity	20
Carton Quantity	20
Pallet Quantity	2100

Product Assets

[Catalog \[English\]](#)