



# YE31LH96, Compression Terminal Plug, Oil/Water Tight with Shroud

By Burndy  
Catalog # [YE31LH96](#)



Oil and water-tight terminal with shrouded, tin-plated,CU barrel and brazed plug Used for terminating insulated CU conductor at cutout or transformer,12.25 IN L.

### Features

- Oil and water-tight terminal with shroud, tin-plated copper barrel and brazed plug
- For terminating insulated copper conductor at cutout or transformer

### Application

Wire Termination

### Specifications

|                               |                      |
|-------------------------------|----------------------|
| Certification - UL Recognized | No                   |
| Buy American Compliant        | Contact Manufacturer |
| Certification - cULus         | No                   |
| EU RoHS Indicator             | Contact Manufacturer |
| Buy America(n) Qualified      | Contact Manufacturer |
| Certification - ETL           | No                   |
| Standards - RoHS Compliance   | CM                   |
| Status                        |                      |
| UL Listed                     | No                   |
| Certification - CSA Approved  | No                   |

### Conductor

|                             |           |
|-----------------------------|-----------|
| Conductor - Material        | COPPER    |
| Conductor - Copper Str Size | 350 KCMIL |
| Conductor - Copper Str      | 350 KCMIL |
| Compact Size                |           |
| Conductor Size              | 350 KCMIL |
| Conductor Type              | CODE      |
| Conductor - Copper Str Size | 350 kcmil |
| Range                       |           |

### Configuration

|                |            |
|----------------|------------|
| Connector Type | INLINE PIN |
|----------------|------------|

### Current

|                   |       |
|-------------------|-------|
| Voltage - Maximum | 35000 |
|-------------------|-------|

### Dimensions

|                               |            |
|-------------------------------|------------|
| Package Height                | 0.000 in   |
| Package Weight                | 0.000 lb.  |
| Package Length                | 0.000 in   |
| Package Width                 | 0.000 in   |
| Dimension - P inch            | 8.06 in    |
| Dimension - L Length Overall  | 311 mm     |
| Dimension - B Length fraction | 2-15/16 in |
| Dimension - B Length inch     | 2.94 in    |
| Dimension - Inside Diameter   | 1.03 in    |
| Dimension - Length BB inch    | 1.25 in    |
| Dimension - Length Overall    | 12.25 in   |
| inch                          |            |

### General

|                        |                        |
|------------------------|------------------------|
| Trade Name             | HYSEALPLUG™            |
| Die Index              | O                      |
| Insulation             | Y                      |
| Feature - Barrel Style | Shrouded               |
| Plated                 | Y                      |
| Sub Brand              | HYSEALPLUG             |
| UPC                    | 781810023402           |
| Type                   | Shrouded Pin Terminals |
| Material               | Copper                 |
| Plating Type           | Tin - Electro Plated   |
| Finish Type            | Tin-Plated             |
| UPC 12 Digit           | 781810023402           |
| UPC 14 Digit GTIN      | 00781810023402         |

### Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 1    |
| Pallet Quantity       | 3360 |
| Carton Quantity       | 20   |

### Operational

|                    |     |
|--------------------|-----|
| Temperature Rating | 194 |
|--------------------|-----|

### Product Assets

[Catalog \[English\]](#)