

YE32R60, Aluminum Terminal Plug

By Burndy
Catalog # [YE32R60](#)



Aluminum HYPLUG with tin-plated copper plug for terminating aluminum or ACSR cable at cutout, transformer and arrestor. Plug can be bent to desired angle.

Features

- Aluminum HYPLUG with tin-plated copper plug for terminating aluminum or ACSR cable at cut-out, transformer and arrestor
- Plug may be bent to desired angle for easier insertion
- Terminals are Pre-Filled with PENETROX A-13 Joint Compound and sealed with color

Application

For Terminating Aluminum Or ACSR Cable At Cut-Out, Transformer And Arrestor

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	• 336.4 (18/1) Merlin kcmil • 336.4 (26/7) Linnet kcmil
Conductor - ACSR Str Size Range	336.4 (18/1) Merlin kcmil-336.4 (26/7) Linnet kcmil
Conductor - AL Str Size	• 350 kcmil • 397 kcmil • 400 kcmil
Conductor - AL Str Size Range	350 kcmil - 400 kcmil

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall	270 mm
Dimension - P inch	6 in
Package Height	0.000 in
Dimension - Length Overall	10.625 in
inch	

General

Die Index	• 317 • 705 • K-1-1/8-1
Trade Name	HYPLUG™
Prefilled Oxide Inhibitor	N
Sub Brand	HYPLUG
Color Code	Green
Plated	Y
Type	YE-R
UPC 12 Digit	781810154403
UPC 14 Digit GTIN	00781810154403
Material	Aluminum
Plating Type	Tin
UPC	781810154403

Logistics

Minimum Pack Quantity	1
Carton Quantity	25
Pallet Quantity	2625

Product Assets

[Catalog \[English\]](#)