



YE34LH119, Compression Terminal Plug, Oil/Water Tight with Shroud, 500 AWG

By Burndy
Catalog # [YE34LH119](#)

Terminal plug, # 500 AWG



Features

- Oil and water-tight terminal with shroud, tin-plated copper barrel and brazed plug
- For terminating insulated copper conductor at cutout or transformer

Application

Wire Termination

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size	500 KCMIL
Conductor - Material	COPPER
Conductor Type	CODE/FLEX
Conductor - Copper Str Size	500 kcmil
Range	
Conductor - Copper Str Size	500 KCMIL

Configuration

Connector Type	INLINE PIN
----------------	------------

Current

Voltage - Maximum	35000
-------------------	-------

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	3-5/16 in

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - P inch	8.06 in
Dimension - L Length Overall	337 mm
mm	
Dimension - B Length inch	3.31 in
Dimension - Inside Diameter	1.14 in
inch	
Dimension - Length BB inch	1.50 in
Dimension - Length Overall	13.25 in
inch	

General

Feature - Barrel Style	Shrouded
Plated	Y
Trade Name	HYSEALPLUG™
Die Index	20
UPC	781810023419
Type	Shrouded Pin Terminals
Insulation	Y
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810023419
UPC 14 Digit GTIN	00781810023419

Logistics

Minimum Pack Quantity	20
Pallet Quantity	1800
Carton Quantity	20

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)