

YE34LH120, Compression Terminal Plug, Oil/Water Tight with Shroud

By Burndy

Catalog # [YE34LH120](#)

Oil and water-tight terminal with shrouded, tin-plated, CU barrel and brazed plug Used for terminating insulated CU conductor at cutout or transformer, 13.25 IN L, Shroud inside dia: 1.88.

Features

- Oil and water-tight terminal with shroud, tin-plated copper barrel and brazed plug
- For terminating insulated copper conductor at cutout or transformer

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	500 KCMIL
Conductor Size	500 KCMIL
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	500 kcmil

Configuration

Connector Type	INLINE PIN
----------------	------------

Current

Voltage - Maximum	35000
-------------------	-------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.



Package Length	0.000 in
Package Width	0.000 in
Dimension - P inch	8.06 in
Dimension - L Length Overall mm	337 mm
Dimension - B Length fraction	3-3/4 in
Dimension - B Length inch	3.76 in
Dimension - Inside Diameter inch	1.88 in
Dimension - Length BB inch	1.50 in
Dimension - Length Overall inch	13.25 in

General

Trade Name	HYSEALPLUG™
Die Index	20
Insulation	Y
Feature - Barrel Style	Shrouded
Plated	Y
Sub Brand	HYPLUG
UPC	781810023426
Type	Shrouded Pin Terminals
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810023426
UPC 14 Digit GTIN	00781810023426

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1800
Carton Quantity	20

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)