



YE361R60, Aluminum Terminal Plug

By Burndy
Catalog # [YE361R60](#)



Aluminum HYPLUG™ Connector, 477, 500 Al 477 (18/1) ACSR, 10-5/8 in L, Terminal Plug for Aluminum and ACSR

Features

- Aluminum HYPLUG with tin-plated copper plug for terminating aluminum or ACSR cable at cut-out, transformer and arrestor
- Plug may be bent to desired angle for easier insertion
- Terminals are Pre-Filled with PENETROX A-13 Joint Compound and sealed with color

Application

For Terminating Aluminum Or ACSR Cable At Cut-Out, Transformer And Arrestor

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	477.0 (18/1) Pelican kcmil
Conductor - ACSR Str Size Range	477.0 (18/1) Pelican kcmil
Conductor - AL Str Size	477 kcmil 500 kcmil
Conductor - AL Str Size Range	477 kcmil-500 kcmil

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - L Length Overall	270 mm
Dimension - P inch	6 in
Package Height	0.000 in
Dimension - Length Overall	10.625 in
inch	

General

Die Index	317 705 - K-1-1/8-1
Trade Name	HYPLUG™
Prefilled Oxide Inhibitor	N
Sub Brand	HYPLUG
Color Code	Pink
Plated	Y
Type	YE-R
UPC 12 Digit	781810154458
UPC 14 Digit GTIN	00781810154458
Material	Aluminum
Plating Type	Tin
UPC	781810154458

Logistics

Minimum Pack Quantity	25
Carton Quantity	25
Pallet Quantity	2100

Product Assets

[Catalog \[English\]](#)