

YE4R25, Aluminum Pin Terminal

By Burndy
Catalog # [YE4R25](#)



Al Compression terminal, #4 #2 #3 AWG 7, 1, 7 str, 4.62"stud,
Orange, BG or 243 index

Features

- Aluminum HYPLUG with tin-plated copper plug for terminating aluminum or ACSR cable at cut-out, transformer and arrestor
- Plug may be bent to desired angle for easier insertion
- Terminals are Pre-Filled with PENETROX A-13 Joint Compound and sealed with color

Application

For Aluminium and ACSR

Specifications

Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - ACSR Str Size	• 4 (6/1) Swan AWG • 4 (7/1) Swanate AWG
Conductor - ACSR Str Size Range	4 (6/1) Swan AWG-4 (7/1) Swanate AWG
Conductor - AL Str Size	• 4 AWG • 3 AWG
Conductor - AL Str Size Range	4 AWG-3 AWG

Dimensions

Package Length	0.000 in
----------------	----------

Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - Outside Diameter	0.65 in
inch	
Dimension - L Length Overall	117 mm
mm	
Dimension - P inch	2.50 in
Package Height	0.000 in
Dimension - Length Overall	4.62 in
inch	

General

Die Index	• K-5/8-1 • 243 • BG • 8A
Trade Name	HYPLUG™
Prefilled Oxide Inhibitor	N
Sub Brand	HYPLUG,PIN TERMINALS
Color Code	Orange
Plated	Y
Type	YE-R
UPC 14 Digit GTIN	00781810154052
Material	Aluminum
Plating Type	Tin
UPC	781810154052

Logistics

Minimum Pack Quantity	1
Carton Quantity	25
Pallet Quantity	24000

Product Assets

[Catalog \[English\]](#)