




YF0215UIL, Bare Ferrule For 2 AWG

By Burndy
Catalog # [YF0215UIL](#)

Bare Ferrule, 2 AWG, 0.59" L



Features

- Made of electrolytic copper, tin plated
- Seamless barrels
- Smooth funnel entry to make wire insertion easier
- RoHS Compliant

Application

For Use On Copper Conductor

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size	2 AWG
Conductor - Copper Solid Size	2 AWG
Conductor - Copper Str Size	2 AWG

Configuration

Connector Type

End Termination

Dimensions

Dimension - D1 inch	0.33 in
Dimension - D2 inch	0.41 in
Dimension - D inch	0.34 in
Dimension - Length Overall	0.59 in

General

Plated	Y
UPC	621945623378
Type	Bootlace Ferrule
Insulation	N
Sub Brand	FERRULES
Material	Copper
Plating Type	Tin - Electro Plated

Logistics

Minimum Pack Quantity	100
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)