




YF0415UIL, Bare Ferrule For 4 AWG

By Burndy
Catalog # [YF0415UIL](#)

Bare Ferrule For 4 AWG



Features

- Made of electrolytic copper, tin plated
- Seamless barrels
- Smooth funnel entry to make wire insertion easier
- UL listed per UL486F requirements
- RoHS Compliant

Application

For Use On Copper Conductor

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Size	4 AWG
Conductor - Copper Solid Size	4 AWG

Conductor - Copper Str Size 4 AWG

Configuration

Connector Type End Termination

Dimensions

Dimension - D1 inch	0.29 in
Dimension - D2 inch	0.37 in
Dimension - D inch	0.30 in
Dimension - Length Overall inch	0.59 in

General

Plated	Y
UPC	621945621633
Type	Bootlace Ferrule
Insulation	N
Sub Brand	FERRULES
Material	Copper
Plating Type	Tin - Electro Plated

Logistics

Minimum Pack Quantity	100
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)