



YF1010IDL, Covered Ferrule For 10 AWG

By Burndy  
Catalog # [YF1010IDL](#)

Covered Ferrule For 10 AWG



Features

- Made of electrolytic copper, tin plated
- Smooth funnel entry to make wire insertion easier
- Secure contacting even after multiple reconnections
- Long-term contact resistance
- No fraying of strands
- No breakage of wire strands when wire is bent, under stress, or in vibration environment
- RoHS Compliant

Application

For Use On Copper Conductor

Specifications

|                               |     |
|-------------------------------|-----|
| Certification - ETL           | No  |
| Certification - UL Recognized | No  |
| Standards - RoHS Compliance   | CM  |
| Status                        |     |
| Certification - cULus         | No  |
| EU RoHS Indicator             | Yes |
| UL Listed                     | No  |
| Certification - CSA Approved  | No  |

Conductor

|                               |        |
|-------------------------------|--------|
| Conductor Size                | 10 AWG |
| Conductor - Copper Solid Size | 10 AWG |
| Conductor - Copper Str Size   | 10 AWG |

Configuration

Connector Type

End Termination

Dimensions

|                            |           |
|----------------------------|-----------|
| Dimension - D1 inch        | 0.14 in   |
| Dimension - D2 inch        | 0.25 in   |
| Dimension - D inch         | 0.15 in   |
| Package Height             | 0.000 in  |
| Package Weight             | 0.000 lb. |
| Package Length             | 0.000 in  |
| Package Width              | 0.000 in  |
| Dimension - Length Overall | 0.71 in   |
| inch                       |           |

General

|              |                      |
|--------------|----------------------|
| Plated       | Y                    |
| UPC          | 621945622388         |
| Type         | Bootlace Ferrule     |
| Insulation   | Y                    |
| Sub Brand    | FERRULES             |
| Material     | Copper               |
| Plating Type | Tin - Electro Plated |

Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 100 |
| Carton Quantity       | 100 |

Product Assets

[Catalog \[English\]](#)