




YF1010ITL, Covered Ferrule For 10 AWG

By Burndy
Catalog # [YF1010ITL](#)

Covered Ferrule For 10 AWG



Features

- Made of electrolytic copper, tin plated
- Smooth funnel entry to make wire insertion easier
- Secure contacting even after multiple reconnections
- Long-term contact resistance
- No fraying of strands
- No breakage of wire strands when wire is bent, under stress, or in vibration environment
- RoHS Compliant

Application

For Use On Copper Conductor

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size	10 AWG
Conductor - Copper Solid Size	10 AWG
Conductor - Copper Str Size	10 AWG

Configuration

Connector Type	End Termination
----------------	-----------------

Dimensions

Dimension - D1 inch	0.14 in
Dimension - D2 inch	0.25 in
Dimension - D inch	0.15 in
Dimension - Length Overall inch	0.71 in

General

Plated	Y
UPC	621945622937
Type	Bootlace Ferrule
Insulation	Y
Sub Brand	FERRULES
Material	Copper
Plating Type	Tin - Electro Plated

Logistics

Minimum Pack Quantity	100
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)