




YF1209IWL, Covered Ferrule For 12 AWG

By Burndy
Catalog # [YF1209IWL](#)

Covered Ferrule For 12 AWG



Features

- Made of electrolytic copper, tin plated
- Smooth funnel entry to make wire insertion easier
- Secure contacting even after multiple reconnections
- Long-term contact resistance
- No fraying of strands
- No breakage of wire strands when wire is bent, under stress, or in vibration environment
- RoHS Compliant

Application

For Use On Copper Conductor

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor Size	12 AWG
Conductor - Copper Solid Size	12 AWG
Conductor - Copper Str Size	12 AWG

Configuration

Connector Type	End Termination
----------------	-----------------

Dimensions

Dimension - D1 inch	0.11 in
Dimension - D2 inch	0.19 in
Dimension - D inch	0.13 in
Dimension - Length Overall inch	0.67 in

General

Plated	Y
UPC	621945621954
Type	Bootlace Ferrule
Insulation	Y
Sub Brand	FERRULES
Material	Copper
Plating Type	Tin - Electro Plated

Logistics

Minimum Pack Quantity	500
Carton Quantity	500

Product Assets

[Catalog \[English\]](#)