




YF1410UIL, Bare Ferrule For 14 AWG

By Burndy
Catalog # [YF1410UIL](#)

Bare Ferrule For 14 AWG



Features

- Made of electrolytic copper, tin plated
- Seamless barrels
- Smooth funnel entry to make wire insertion easier
- UL listed per UL486F requirements
- RoHS Compliant

Application

For Use On Copper Conductor

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Size	14 AWG
Conductor - Copper Solid Size	14 AWG
Conductor - Copper Str Size	14 AWG

Configuration

Connector TypeEnd Termination

Dimensions

Dimension - D1 inch	0.09 in
Dimension - D2 inch	0.13 in
Dimension - D inch	0.10 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Length Overall	0.39 in
inch	

General

Plated	Y
UPC	621945621381
Type	Bootlace Ferrule
Insulation	N
Sub Brand	FERRULES
Material	Copper
Plating Type	Tin - Electro Plated

Logistics

Minimum Pack Quantity	1000
-----------------------	------

Product Assets

[Catalog \[English\]](#)