YF1607UIL, Bare Ferrule For 16 AWG



By Burndy
Catalog # YF1607UIL

Bare Ferrule For 16 AWG

Features

- Made of electrolytic copper, tin plated
- Seamless barrels
- Smooth funnel entry to make wire insertion easier
- UL listed per UL486F requirements
- RoHS Compliant

Application

For Use On Copper Conductor

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Size	16 AWG
Conductor - Copper Solid Size	16 AWG
Conductor - Copper Str Size	16 AWG

Configuration

Connector Type	End Termination

Dimensions

Dimension - D1 inch	0.07 in
Dimension - D2 inch	0.11 in
Dimension - D inch	0.08 in
Dimension - Length Overall inch	0.28 in

General

Plated	Y
UPC	621945621589
Type	Bootlace Ferrule
Insulation	N
Sub Brand	FERRULES
Material	Copper
Plating Type	Tin - Electro Plated

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000

Product Assets

Catalog [English]

© 2026 Hubbell Incorporated. All rights reserved