



Ratchet Ferrule Crimper, Side Load Capability with (3) Interchangeable Dies, Use with Bare and Covered UL Listed Ferrule Series, #26 AWG - 1/0 AWG.

By Burndy
Catalog # [YF261CSKIT](#)

Ratchet Ferrule Crimper, Dies, #26-1/0 AWG

Features

- Side Load
- Low handle force to reduce strain
- Crimps Bare and Covered Ferrules
- Left and Right Hand Compatible
- Full Cycle Ratchet with non-slip handles
- Interchangeable Dies: YF2610D (26-10), YF864D (8,6,4) YF21D (2,1,1/0)

Application

Crimping

Conductor

Crimping Ranges Copper: #26 AWG - #1/0 AWG

Dimensions

Weight 1.25 lb.



Height	0.9 in
Width	2.7 in
Length	10 in
Dimensions	10 in x 2.7 in x 0.9 in

General

Tool Type	Ratchet Crimper for Ferrules
Application - For Use On	Bare and Covered Ferrules
UPC	621945625938
Type	Crimper

Logistics

Package Contents	Tool, YF2610D, YF864D, YF21D, torque key, plastic case
------------------	--

Product Assets

[Catalog \[English\]](#)