



Ratchet Ferrule Crimper with Front and Side Load Capability, Use with Bare and Covered UL Listed Ferrule Series, #26 AWG - 8 AWG.

By Burndy
Catalog # [YF268CFSL](#)

Ratchet Ferrule Crimper, #26-8 AWG

Features

- Front or Side Load
- Ergonomic Design
- Crimps Bare and Covered Ferrules
- Left and Right Hand Compatible
- Full Cycle Ratchet with non-slip handles
- Self-adjusting for covered and bare ferrules

Application

Crimping

Specifications

Buy America(n) Qualified	TAA Compliant (All status valid till December 2026)
--------------------------	---

Conductor

Crimping Ranges	Copper: #26 AWG - #8 AWG
-----------------	--------------------------



Dimensions

Weight	0.65 lb.
Height	0.9 in
Width	2.7 in
Length	7.1 in
Dimensions	7.1 in x 2.7 in x 0.9 in

General

Tool Type	Ratchet Crimper for Ferrules
Application - For Use On	Bare and Covered Ferrules
UPC	621945625921
Type	Crimper

Logistics

Package Contents	Tool only
------------------	-----------

Product Assets

[Catalog \[English\]](#)