




YFM28CR, Copper - Cable To Mole Limiter

By Burndy
Catalog # [YFM28CR](#)



Limiter Lug Assembly, 4/0 Str, For Rubber Insulated Cables

Features

- Copper Cable to Mole Limiter Lug Assembly
- With Shell and Rubber Sleeve for Insulated Cables

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	4/0 AWG
-----------------------------	---------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Dimension - F Width Center to Center inch	1.89 in
Dimension - AA Pad	1.34 in
Orientation	
Package Width	0.000 in
Dimension - B Length inch	1.86 in
Dimension - Outside Diameter inch	2.38 in

Dimension - D inch	6.22 in
Dimension - Length BB inch	3.06 in
Dimension - Length Overall inch	11.5 in
Dimension - Strip Length inch	2.5 in

General

Plated	N
Color Code	Purple
Insulation Type	Rubber
Trade Name	MOLIMITER™
Die Index	15
UPC	781810000861
Insulation	Y
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810000861
UPC 14 Digit GTIN	00781810000861

Logistics

Minimum Pack Quantity	1
Pallet Quantity	500
Carton Quantity	10

Product Assets

- [Catalog \[English\]](#)
[Installation Manual \[English\]](#)