


YFM34CPL, Copper - Cable To Mole Limiter

By Burndy
Catalog # [YFM34CPL](#)



Long Limiter Lug Assembly, 500 kcmil, For Paper Lead Cables

Features

- The Long MOLIMITER differs from the Standard MOLIMITER only in its extra long cable socket

Application

For Paper-Lead Cables

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	500 kcmil
-----------------------------	-----------

Dimensions

Dimension - F Width Center to Center inch	1.89 in
Dimension - AA Pad Orientation	1.34 in
Dimension - B Length inch	2.75 in
Dimension - Outside Diameter inch	2.38 in

Dimension - D inch	8.26 in
Dimension - Length BB inch	4.31 in
Dimension - Length Overall inch	11.5 in
Dimension - Strip Length inch	3.25 in

General

Plated	N
Color Code	Brown
Insulation Type	Paper
Trade Name	MOLIMITER™
Sub Brand	NETWORK UNDERGROUND, MOLIMITER
Die Index	20
UPC	781810000885
Type	YFM-CPL, Long
Insulation	Y
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810000885
UPC 14 Digit GTIN	00781810000885

Logistics

Minimum Pack Quantity	1
Pallet Quantity	400
Carton Quantity	8

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)