



YFMR28, Copper - Link Limiter

By Burndy
Catalog # [YFMR28](#)

For Use with MOLIMITER™ Assembly.



Features

- Copper Link Limiter for use with MOLIMITER Assembly

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size	4/0 AWG
Range	
Conductor - Copper Str Size	4/0 AWG

Configuration

Connector Type	Limiter
----------------	---------

Dimensions

Dimension - B Length fraction	1-7/8 in
Dimension - B Length inch	1.86 in
Dimension - Outside Diameter	0.83 in

Dimension - Inside Diameter	0.55 in
Dimension - Length Overall	6.28 in

General

Plated	Y
Trade Name	MOLIMITER™
UPC	781810262337
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810262337
UPC 14 Digit GTIN	00781810262337

Logistics

Minimum Pack Quantity	50
Pallet Quantity	12000
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)