

YFS28CR, Copper - Cable To Cable Limiter

By Burndy
Catalog # [YFS28CR](#)



Limiter Assembly, 4/0 Str, 250 V, For Rubber Insulated Cables

Features

- Copper Cable to Cable Limiter
- For Rubber Insulated Cables

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	4/0 AWG
Conductor - Copper Str Size	4/0 AWG

Configuration

Connector Type	Limiter
----------------	---------

Dimensions

Dimension - Pad Width inch	2.38 in
Dimension - F Width Center to Center inch	1.89 in

Dimension - B Length inch	1.72 in
Dimension - D inch	8.94 in
Dimension - Length Overall inch	15.69 in
Dimension - Strip Length inch	2.5 in

General

Plated	N
Color Code	Purple
Insulation Type	Rubber
Die Index	15
UPC	781810000892
Insulation	Y
Plating Type	Unplated
UPC 12 Digit	781810000892
UPC 14 Digit GTIN	00781810000892

Logistics

Minimum Pack Quantity	1
Pallet Quantity	120
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[English\]](#)