



YFSP28L, Limiter Link, Long Barrel

By Burndy
Catalog # YFSP28L

LIMITER LINK LONG BARREL



Features

- Limiter Link, Long Barrel

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	350 kcmil
Conductor - AL Str Size Range	350 kcmil

Configuration

Connector Type	Limiter
----------------	---------

Dimensions

Dimension - Pad Width inch	2.91 in
Dimension - B Length fraction	2-15/16 in
Dimension - F Width Center to Center inch	0.21 in

Dimension - B Length inch	1.38 in
Dimension - Outside Diameter inch	0.69 in
Dimension - D inch	0.16 in
Dimension - N inch	0.81 in
Dimension - Inside Diameter inch	0.55 in
Dimension - Length Overall inch	8.75 in

General

Feature - Barrel Style	Chamfered
Plated	N
UPC	781810196007
Plating Type	Unplated
UPC 12 Digit	781810196007
UPC 14 Digit GTIN	00781810196007

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3360
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)