



YG14BTC28 Compression Bus Bar Connector

By Burndy
Catalog # [YG14BTC28](#)



Copper Compression Bus Bar Connector, 1/8 " Thick Steel and Copper Busbar to 4/0 AWG - 1/0 AWG Str

Features

- Compression Busbar Connector
- Easier to use than Exothermic Connections
- Ideally suited for cellular tower applications.

Application

For Direct Barial And Cellular Tower Applicatons And Is Easier To Use Than Exothermic Connections

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	Yes
Industry Standard(s)	• UL467 • UL 486A • CSA C22.2 No 65
Certification - ETL	No
Standards - Industry Standards Met	• UL467 • UL 486A • CSA C22.2 No 65
Standards - RoHS Compliance Status	CM
Certification - UL Listed Direct Burial	Yes
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Run	1/8" - 1/4" Busbar
Conductor - Copper Solid Tap Range	4/0 AWG
Conductor - Copper Solid Tap	4/0 AWG
Conductor Type	• CU C Str-Size • CU C Solid-Size • Bar-Size
Conductor - Copper Str Tap Range	1/0-4/0
Conductor - Copper Str Tap	• 1/0 • 2/0 AWG • 3/0 AWG

- 4/0 AWG

Configuration

Physical Attribute - Number of Crimps Required	1
Connector Type	Tap

Dimensions

Dimension - Pad Width inch	1.50 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length fraction	64/79 in
Dimension - B Length inch	0.81 in
Dimension - Bus Bar Size Tap Side inch	4/0 AWG Str. to 1/0 AWG Str. Copper

General

Trade Name	HYGROUND®
Prefilled Oxide Inhibitor	Y
Plated	No
Sub Brand	HYGROUND
Product Type	Compression
UPC	781810289273
Type	YG-B
Material	Copper Alloy
Plating Type	Unplated
UPC 12 Digit	781810289273
UPC 14 Digit GTIN	00781810289273

Logistics

Minimum Pack Quantity	1
Pallet Quantity	5800
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)