



YGA282NTN Comp Ground Lug, 4/0 AWG Cu, 2-Hole NEMA, Tinned

By Burndy
Catalog # [YGA282NTN](#)

HYLUG™ Copper Compression Terminal for Grounding; 2-Hole



Features

- Irreversible compression ground terminal specifically designed for grounding applications
- UL467 Listed
- Acceptable for Direct Burial in earth or concrete
- Prefilled with PENETROX oxide inhibitor compound

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor - Copper Str Size Range	4/0 AWG
Conductor - Copper Str Size	4/0 AWG

Configuration

Physical Attribute - Number of Crimps Required	2
Connector Type	Terminal

Dimensions

Dimension - Pad Width inch	1.00 in
Dimension - Bolt Hole Size inch	0.52 in
Package Height	0.000 in
Dimension - B Length fraction	1-4/7 in

Package Weight	0.000 lb.
Dimension - Width inch	0.53 in
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	131 mm
Dimension - B Length inch	1.57 in
Dimension - Outside Diameter inch	0.69 in
Dimension - Width fraction	1/2 in
Dimension - N inch	0.62 in
Dimension - Hole Size mm	14 mm
Dimension - Bolt Size inch	0.50 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	5.17 in
Dimension - Strip Length inch	1-11/16
Dimension - Stud Size inch	1/2

General

Plated	Y
Color Code	Purple
Trade Name	HYLUG™
Die Index	15
UPC	781810236079
Type	Terminals
Material	Copper
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810236079
UPC 14 Digit GTIN	00781810236079

Logistics

Minimum Pack Quantity	1
Pallet Quantity	9600
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)