

YGA2C2TC38E2G1 Compression Grounding Lug

By Burndy
Catalog # [YGA2C2TC38E2G1](#)

Grounding Irreversible Compression Terminals.



Features

- Irreversible compression ground terminal specifically designed for grounding applications
- Each connector has an inspection probe hole to ensure proper cable insertion
- UL467 Listed
- Acceptable for Direct Burial in earth or concrete
- UL486A Listed
- Prefilled with PENETROX™ compound and strip sealed

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	• UL467 • UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - UL Listed Direct Burial	Yes
Industry Standard(s)	• UL467 • UL 486A-486B
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Solid Size	2 AWG
Conductor - Copper Solid Size Range	2 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor - Copper Str Size Range	2 AWG
Conductor - Copper Str Size	2 AWG

Configuration

Connector Type	Terminal
----------------	----------

Dimensions

Dimension - Pad Width inch	0.60 in
Dimension - Bolt Hole Size inch	0.39 in
Package Height	0.000 in
Dimension - B Length fraction	1-1/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	93 mm
Dimension - B Length inch	1.25 in
Dimension - Outside Diameter inch	0.42 in
Dimension - N inch	0.62 in
Dimension - Hole Size mm	10 mm
Dimension - Bolt Size inch	0.38 in
Dimension - Hole Size inch	0.40 in
Dimension - Length Overall inch	3.66 in
Dimension - Strip Length inch	1 in
Dimension - Stud Size inch	3/8

General

Plated	N
Color Code	Brown
Trade Name	HYLUG™
Die Index	10
UPC	781810109632
Type	Terminals
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810109632
UPC 14 Digit GTIN	00781810109632

Logistics

Minimum Pack Quantity	25
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)